progress lighting DESIGN**+SERIES**™

Project:			
Fixture Type:			
Location:			
Contact:			

P560006-169 Union Square

Union Square One-Light Large Antique Copper Urban Industrial Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Copper (Painted) with Matte Black accent Construction: Steel Construction Glass/Shade: Clear Glass Panel



Width: 9-3/4 in Extends: 8 in Height: 23-5/8 in H/CTR: 9-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 7" W., 0.81" ht., 7" depth		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	