

| DATE: | TYPE: | |
|----------|-------|--|
| NAME: | | |
| PROJECT: | | |



P560011-031

Kiawah

Enjoy the updated classic styling for a variety of outdoor applications in the Kiawah collection. The two-light wall lantern features seeded glass panels and traditional detailing combine to create a soft and updated lantern design. Hinged door for easy relamping.

- Black finish
- Updated classic style
- Seeded glass panels with traditional detailing
- Easy access for relamping

Category: Outdoor

Finish: Black (Powdercoat)

Construction: Aluminum construction **Glass/Shade:** Clear seeded glass panels



Width: 7-1/2" Height: 21-7/8" Depth: 8-3/8"

H/CTR: 8-1/4" (facing up)

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---|---|--|
| Wall mounted Mounting strap for outlet box included Backplate covers a standard 4" hexagonal recessed outlet box 4.5" W., 9.25" ht., 0.75" depth | Pre-wired 6" of wire supplied 120 V | Quantity: Two 60w max. Candelabra Base E12 base phenolic socket | cCSAus Wet location listed 1 year warranty |
| | | | |