## progress lighting DESIGN**+SERIES**™

Project:	
Fixture Type:	
Location:	

Contact:

## P560021-031 Gibbes Street

Incorporate a flawless lighting experience that fills your home with an understated elegance and rustic charm with this wall lantern. This farmhouse-inspired masterpiece cradles clear beveled glass panes just right for offering a warm, welcoming glow to your friends and family. A traditional lantern frame with a beautiful black finish houses the light bases in this timeless design.

- This farmhouse-inspired masterpiece cradles clear beveled glass panes just right for offering a warm, welcoming glow to your friends and family.
- A traditional lantern frame with a beautiful black finish houses the light bases in this timeless design.
- Incorporate a flawless lighting experience that fills your home with an understated elegance and rustic charm with this wall lantern.
- · Ideal for any bedroom, foyer, entryway, porch, or patio.
- Perfect for transitional or new traditional settings.
- Measures 5-1/2-inch width by 15-1/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted) Construction: Cast Aluminum Construction Glass/Shade: Clear Beveled glass Panel



Width: 5-1/2 in Height: 15-1/8 in Depth: 7 in H/CTR: 5-7/8 in

Clear Beveled glass Panel Width: 4-3/4 in Height: 7-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5"			

ht., 0.812" depth