

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P560032-031

Creighton

A cottage-inspired outdoor wall lantern collection with a tapered cage. Creighton features clear water glass clear and Black finish. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.

- Black finish
- Cottage-inspired outdoor lantern
- Features a tapered cage design
- Clear water glass panels
- Linear details enhance mechanical detailing of fixture

Category: Outdoor Finish: Black (painted)

Construction: Aluminum construction **Glass/Shade:** Clear water glass panels



Width: 8-3/8" Height: 15-3/4" Depth: 9-3/8"

H/CTR: 3" (facing up)

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	cCSAus Wet location listed
Mounting strap for outlet box included Backplate covers a standard 4" hexagonal recessed outlet box 4.5" W., 7.0625" ht., 1" depth	6" of wire supplied 120 V	One 100w max. Medium Base E26 base ceramic socket	1 year warranty