## PROGRESS LIGHTING<sup>™</sup>

Project:			
Fixture Type:			
Location:			
_			

Contact:

## P560057-31M Gunther

Gunther One-Light Matte Black Modern Farmhouse Medium Wall Lantern

Category: Outdoor Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 6-1/2 in Extends: 7-3/4 in Height: 9-1/2 in H/CTR: 2-3/4 in

Clear Glass Cylindrical Width: 5 in Height: 7-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.5" W., 0.75" ht., 5.5" depth		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	