

Project:			
Fixture Type:			
Location:			
Contact:			

P560058-31M

Gunther

Gunther One-Light Matte Black Modern Farmhouse Large Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Width: 8 in Extends: 9-1/4 in Height: 11-1/2 in H/CTR: 3-3/8 in

Clear Glass Cylindrical

Width: 6 in Height: 9-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Back Plate covers a standard 4"		socket	
recessed outlet box: 6.75" W., 0.875" ht., 6.75" depth		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	