



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P560083-103

Conover

Conover is an outdoor lantern collection featuring nautical influences. A protective die cast ring surrounds beautiful clear seeded glass. Vintage metallic finishes are available for this collection that is sure to enhance curb appeal for a variety of exteriors.

- An outdoor lantern collection featuring nautical influences
- Vintage metallic finish enhance curb appeal for a variety of exteriors
- Antique Pewter finish
- Wall lantern uses one 100-watt max. medium base bulbs (sold separately)
- A protective die cast ring surrounds beautiful clear seeded glass
- Outdoor lanterns add illumination to walkways and pathways to enhance safety and security
- Add to either side of front door to welcome guests and visitors to the home
- Outdoor lanterns can also be paired with decorative indoor fixtures to create a customized and creative lighting design

Width: 7"
Height: 14-1/4"
Depth: 9"
H/CTR: 7-1/2"

Glass
Width: 6-1/8"
Height: 7-7/8"

Category: Outdoor

Finish: Antique Pewter (painted)

Construction: Aluminum

Glass/Shade: Clear Seeded Glass shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box 4.75" W., 6.375" ht., 0.875" depth	6" of wire supplied 120 V	Quantity: One 100w max. medium E26 base	cCSAus Wet location listed 1 year limited warranty