



DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

## P560084-020

## Conover

Conover is an outdoor lantern collection featuring nautical influences. A protective die cast ring surrounds beautiful clear seeded glass. Vintage metallic finishes are available for this collection that is sure to enhance curb appeal for a variety of exteriors.

- An outdoor lantern collection featuring nautical influences
- Vintage metallic finish enhance curb appeal for a variety of exteriors
- Antique Bronze finish
- Wall lantern uses one 100-watt max. medium base bulbs (sold separately)
- A protective die cast ring surrounds beautiful clear seeded glass
- Outdoor lanterns add illumination to walkways and pathways to enhance safety and security
- Add to either side of front door to welcome guests and visitors to the home
- Outdoor lanterns can also be paired with decorative indoor fixtures to create a customized and creative lighting design

Category: Outdoor

Finish: Antique Bronze (painted)
Construction: Aluminum

Glass/Shade: Clear Seeded Glass shade



Width: 8-5/8" Height: 16" Depth: 10-1/4" H/CTR: 7-5/8"

Glass

Width: 7-3/4" Height: 9-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6" of wire supplied	Quantity:	cCSAus Wet location listed
Mounting strap for outlet box included  Back plate covers a standard 4" octagonal recessed outlet box  5.375" W., 6.5" ht., 1" depth	120 V	One 100w max. medium E26 base	1 year limited warranty