PROGRESS LIGHTING

Project:		
Fixture Type:		
Location:		

Contact:

P560087-028 Gables

Gables Collection One-Light Coastal Satin White Outdoor Wall Lantern with $\ensuremath{\mathsf{DURASHIELD}}$

Category: Outdoor

Finish: Satin White (Unfinished) Construction: injection-Molded Plastic Construction Glass/Shade: Clear Glass Cylindrical



Width: 5-7/8 in Extends: 6-7/8 in Height: 11-3/4 in H/CTR: 7-5/8 in

Clear Glass Cylindrical Width: 4-3/4 in Height: 8-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	5-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.75" W., 6.25" ht., 1" depth		LED: 12.5-watt MAX per socket	
· •		Fully dimmable with dimmable bulbs	