

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560088-020

Gables

Gables Collection Outdoor Wall Lantern with DURASHIELD

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear Glass Cylinder



Width: 7-1/2 in
Depth: 8-1/2 in
Height: 14-1/8 in
H/CTR: 10-1/4 in

Clear Glass Cylinder
Width: 5-7/8 in
Height: 10-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Lamp Type A19	cCSAus Wet Location Listed
Mounting strap for outlet box included	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	5-year Limited Warranty
back plate covers a standard 4" recessed outlet box: 4.75" W., 7" ht., 0.875" depth		Fully dimmable with dimmable bulbs.	