



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560088-028 Gables

Gables Collection One-Light Coastal Satin White Outdoor Wall Lantern with DURASHIELD

Category: Outdoor

Finish: Satin White (Unfinished)

Construction: injection-Molded Plastic Construction

Glass/Shade: Clear Glass Cylindrical



Width: 7-1/2 in
 Extends: 8-1/2 in
 Height: 14-1/8 in
 H/CTR: 10-9/16 in

Clear Glass Cylindrical
 Width: 5-7/8 in
 Height: 10-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 6.25" ht., 1" depth		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
		Fully dimmable with dimmable bulbs	