

| Project: | | |
|---------------|--|--|
| Fixture Type: | | |
| Location: | | |
| Contact: | | |

P560091-031 Cedar Springs

This fun take on the traditional warehouse shade provides excellent task lighting for reading a book or illuminating a doorway. Take in the simple metal shade coated in a gorgeous black finish ready to direct a helpful glow. An industrial-style wall plate anchors the light fixture in place and adds a touch of urban flair.

- Take in the simple metal shade coated in a gorgeous black finish ready to direct a helpful glow.
- An industrial-style wall plate anchors the light fixture in place and adds a touch of urban flair.
- This fun take on the traditional warehouse shade provides excellent task lighting for reading a book or illuminating a doorway.
- Ideal for any foyer, entryway, bedroom, sitting room, porch, or patio.
- · Perfect unban industrial, rustic, farmhouse, and coastal settings.
- Measures 13-1/4-inch width by 11-1/4-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Aluminum Construction



Width: 13-1/4 in Height: 11-1/4 in Depth: 21-5/8 in H/CTR: 7-1/4 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|---------------------------|--|----------------------------|
| Wall mounted | Prewired | Quantity: One 100 W max. Medium Base or | CCSAus Wet Location Listed |
| Mounting plate for outlet box included | 6 inches of wire supplied | LED equivalent | 1-year Limited Warranty |
| | 120 V | E26 base Porcelain socket | |
| Back Plate covers a standard 4" recessed outlet box: 5" W., 2.25" ht., 5" depth | | | |