

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P560098-031

Englewood

Inspired by the warmth and beauty of hammered copper home accents, Englewood's design displays elements of rustic craftsmanship. A one-light medium wall lantern in Black with the inside of the shade that features a metallic copper coating of paint, offering higher illumination reflection. Ideal for Farmhouse architecture design styles. Perfect for interior or exterior applications.

- Inspired by the look of hammered copper Englewood fixtures display elements of rustic craftsmanship
- An interior coating of copper metallic paint amplifies its illumination
- The medium wall lantern can be hung on either side of a front or rear door, by a garage, on exterior walls or in porches or outdoor living areas, or in casual living rooms, dining rooms, kitchens and bathrooms
- Perfect for Farmhouse interior and exterior architecture
- Deep Black finish
- Measures 12in diameter x 10 3/8in ht.
- Uses one 100-watt max. medium base bulb or LED equivalent (sold separately)
- Dark Sky compliant
- UL Safety listed for use in wet locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Outdoor

Finish: Black (painted)

Construction: Steel Construction



Diameter: 12"
Height: 10-3/8"
Depth: 13-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted covers a standard 4" octagonal recessed outlet box 4.625" W., 1.25" ht., 4.625" depth	6" of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base porcelain socket	cCSAus Wet location listed 1 year warranty