

DATE:

TYPE:

NAME:

PROJECT:

Incandescent

P560103-020

River Place

River Place one-light small wall lantern showcases an inviting design to create instant curb appeal for the home. The clear seeded glass is topped with a flared roof, resembling the features of a pineapple, the symbol of hospitality. An Antique Bronze finish completes the lantern with a graceful touch of tradition.

- These outdoor lanterns channel the shape of a pineapple, the beloved symbol of hospitality
- The flared, fluted roof of these fixtures are encased in clear seeded glass
- The large wall lantern makes a cheerful greeting on either side of an entry door, flanking an outdoor fireplace or hanging on the walls of a covered outdoor living area
- River Place's construction and Southern-influenced design is a perfect addition to Traditional and Coastal homes
- Rich Antique Bronze finish
- Measures 9 1/4in W x 24 1/8in ht.
- Uses one medium base bulb, 100-watt max., and are perfectly compatible with a wide variety of bulbs including LED, Vintage ST64 and more (all sold separately)
- UL Safety listed for use in wet locations
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Outdoor

Finish: Antique Bronze (plated)

Construction: Aluminum Construction

Glass/Shade: Clear Seeded Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted covers a standard 4" octagonal recessed outlet box 4.5" W., 8" ht., 1" depth	6" of wire supplied 120 V	Quantity: One 100w max. Medium Base E26 base porcelain socket	cCSAus Wet location listed 1 year warranty



Diameter: 9-1/4" Height: 24-1/8" Depth: 9-5/8"

Glass Width: 4-3/16" Height: 11-1/4"