

DATE:

TYPE:

NAME:

PROJECT:

Incandescent

## P560117-103

## Morrison

The Morrison Collection medium wall lantern blends delicate geometric patterns with lasting durability in a modern form. Intricate die cast aluminum construction is paired with clear glass and an Antique Pewter finish.

- Swirling metallic accents covering a clear-glass shade are an ornamental addition to your home's exterior
- The medium wall lantern makes a cheerful greeting on either side of an entry door, flanking an outdoor fireplace or hanging on the walls of a covered outdoor living area
- Morrison's construction and design complements both Modern and Traditional architecture
- Stately Antique Pewter finish
- Measures 7 1/2in W x 21 3/8 ht.
- Uses one 100-watt max. medium base bulb including LED equivalent (sold separately)
- UL Safety listed for use in wet locations
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

## Category: Outdoor

Finish: Antique Pewter (plated)

**Construction:** Die-cast aluminum Construction

## Glass/Shade: Clear cylinder

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6" of wire supplied	Quantity:	cCSAus Wet location listed
covers a standard 4" octagonal recessed outlet box 5" W., 10.75" ht., 1" depth	120 V	One 100w max. Medium Base E26 base porcelain socket	1 year warranty
5 W., 10.75 HL, 1 deput			

-1/2"

Diameter: 7-1/2" Height: 21-3/8" Depth: 9-1/4"

Glass Width: 5-7/8" Height: 11-7/16"