progress lighting DESIGN**+SERIES**™

Project:			
Fixture Type:			
Location:			
Contact:			

P560123-108 Janssen

Create a home full of modern elegance with this contemporary wall lantern. A sleek elongated frame with a rectangular form manifests an architectural design intended to add a modern glow while commanding visual interest. The light fixture features a gorgeous etched glass diffuser ready to emit a beautiful glow.

- The light fixture features a gorgeous etched glass diffuser ready to emit a beautiful glow.
- A sleek elongated frame with a rectangular form manifests an architectural design intended to add a modern glow while commanding visual interest.
- Create a home full of modern elegance with this contemporary wall lantern.
- · Ideal for any bedroom, foyer, entryway, porch, or patio.
- Perfect for casual, contemporary, or modern styles.
- Measures 7-1/2-inch width by 19-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Oil Rubbed Bronze (Painted) Construction: Aluminum Construction Glass/Shade: Etched glass Cylindrical Shade

ht., 0.75" depth



Width: 7-1/2 in Height: 19 in Depth: 8-1/4 in H/CTR: 5 in

Etched glass Cylindrical Shade Width: 4-1/2 in Height: 12 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 10"			