

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P560135-020

Westport

The Westport Collection offers transitional styling to complement a variety of architectural exteriors. A durable die-cast aluminum frame cradles a softly diffused seeded glass shade. The two-light medium wall lantern is finished in Antique Bronze.

- Iconic carriage-house design
- The two-light wall lantern is suited for placement at a front or back door, along exterior walls or within an covered outdoor living area
- Westport is a natural fit for Traditional and Transitional architecture
- Classic Black finish
- Measures 11in W x 19 3/8in ht.
- Uses two 60-watt max. candelabra base bulbs or LED equivalent (sold separately)
- UL Safety listed for use in wet locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Outdoor

Finish: Antique Bronze (plated)

Construction: Die-cast aluminum Construction

Glass/Shade: Clear Seeded Cylindrical



Diameter: 11"
Height: 19-3/8"
Depth: 12-7/8"

Glass
Width: 8-1/2"
Height: 7"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted covers a standard 4" octagonal recessed outlet box 6.75" W., 9.25" ht., 1" depth	6" of wire supplied 120 V	Quantity: Two 60w max. Candelabra Base E12 base phenolic sockets	cCSAus Wet location listed 1 year warranty