

Project:		
Fixture Type:		
Location:		
Contact:		

LED Wall Lantern

Wall mounted • Wet location listed PROGRESS LED

Description:

This energy efficient LED wall lantern features a Black finish on a die-cast aluminum frame. This fixture includes integrated LED technology with no bulbs to replace. The frosted glass panels have a warm quality that adds to the lantern's traditional design.

Specifications:

- · Black (-031) (painted)
- · Die-Cast Aluminum Construction
- · Etched glass Panels
- · This energy efficient LED wall lantern features a die-cast aluminum frame
- · This fixture includes integrated LED technology
- · Features frosted glass panels
- The one-light wall lantern is suited for placement at a front or back door, along exterior walls or within an covered outdoor living area
- Measures 5-5/8in dia. x 8-7/8in ht.
- 11w integrated LED, 564 delivered lumens 47 lumens/watt (delivered) 3000K color temperature, 80+ CRI.
- · CSA Safety listed for use in wet locations
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality
- · Includes installation instructions and mounting hardware
- · Back plate covers a standard 4" octagonal recessed outlet box
- · Mounting swivel mounting strap for outlet box included
- 6" of wire supplied
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1	
Input Power	11w	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW (Delivered)	564/47 (LM-79)	
ССТ	3000 K	
CRI	82 CRI	
Life (hours)	36,000 (L70/TM-21)	
FCC	FCC Title 47, Part 15, Class B	
Min. Start Temp	-30 °C	
Max. Operating Temp	-30°C	
Warranty	5 year limited warranty	
Labels	cCSAus Wet location listed	
	Meets California Title 24 high efficacy requirements	
	for outdoor use only	

P560136-031-30

Images:



Dimensions:

Square: 5-5/8" Depth: 6-5/8" Height: 8-7/8" H/CTR: 6-5/8"

Etched glass panels Width: 4-3/16" Height: 4-1/2"