

Project:

Fixture Type:

Location:

Contact:

Z-1090 LED

Wall Mounted · Wet Location Listed PROGRESS LED



Description:

An elongated frame and clean, crisp lines are the hallmarks of this striking light fixture. A modern take on an open-cage design is manifested by a rectangular silhouette with an open bottom and sides through which a stunning glow can shine. At the fixture's crown, a solid square attaches to the simple backplate for a final punctuated dash of formal elegance. A bold, black finish completes the stately design sure to elevate your home decor style.

Specifications:

- •
- A modern take on an open-cage design is manifested by a rectangular silhouette with an open bottom and sides through which a stunning glow can shine.
- A bold, black finish completes the stately design sure to elevate your home décor style.
- At the fixture's crown, a solid square attaches to the simple backplate for a final punctuated dash of formal elegance.
- Ideal for any bedroom, foyer, entryway, porch, or patio.
- · Perfect for transitional, modern, and contemporary settings.
- Measures 4-1/2-inch width by 16-inch height.
- Uses one LED module (9w).
- Compatible with many Triac/ELV dimmers (see dimming controls)
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.5 in W., 5 in ht., 0.812 in depth
- + Mounting backplate for outlet box included
- 6 in of wire supplied

Performance:


Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
ССТ	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	ENERGY STAR [®] qualified
	Meets California Title 24 JA8-2016


P560137-031-30



Dimensions:

Width: 4-1/2 in Height: 16 in Depth: 4-3/8 in H/CTR: 2-1/2 in







Z-1090 LED

Wall Mounted • Wet Location Listed PROGRESS LED



Dimming Notes:

P560137-031-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron Diva DVELV-300P	
Lutron Nova T NTELV-300	
Lutron Caseta	
Lutron Ariadni AY-600P	
Leviton Illumatech IPI06-1LZ	
Leviton SureSlide 6672	
Lutron Ariadni AYCL-153P	
Lutron Skylark Contour CTCL-153P	
Lutron Diva DVCL-153P	
Lutron Toggler TGCL-153P	
Lutron Maestro MACL-153M	
Lutron Ariadni AYLV-600P	
Lutron NOVA T NTLV-600	
lutron Maestro MAELV-600	
Lutron spacer/system SPSELV-600	
Lutron Renoir II AWRMG-EAW	
Lutron Nova N-600	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P560137-031-30