

Project:			
Fixture Type:			
Location:			
Contact:			

## P560149-031

## **Irondale**

Incorporate memorable modern lighting with the industrial Irondale Collection's One-Light Black Wall Lantern. A matte black frame attaches to a rectangular wall plate. A clear glass shade holds an etched glass diffuser ready to provide a lovely ambient glow.

- · Matte black frame attaches to a rectangular wall plate.
- · A clear glass shade holds an etched glass diffuser ready to provide a lovely ambient glow.
- · Modern light fixture with an industrial flair.
- Ideal for any foyer, bedroom, entryway, porch, or patio.
- Perfect for urban industrial or Craftsman settings.
- · Measures 7-7/8-inch width by 15-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

**Construction:** Steel Construction

Glass/Shade: Clear glass Curved Panel, Etched White glass Cylindrical



Width: 7-7/8 in Height: 15-1/2 in Depth: 8-1/2 in H/CTR: 13 in

Clear glass Curved Panel

Width: 6-1/4 in Height: 12 in

Etched White glass Cylindrical

Width: 4-5/16 in Height: 12-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 9" ht., 0.75" depth			