

Project: Fixture Type: Location: Contact:

P560151-020 **Oakcliff**

This wall lantern is a fine illustration of how rustic style can be comfortable and contemporary. The light fixture features a cabin-inspired design with a handsome antique bronze frame. The frame holds an etched seeded glass shade ready to produce a gentle, modern mountain glow just right for your favorite lodge escape.

- The light fixture features a cabin-inspired design with a handsome antique bronze frame.
- The frame holds an etched seeded glass shade ready to produce a gentle, modern mountain glow just right for your favorite lodge escape.
- This wall lantern is a fine illustration of how rustic style can be comfortable and contempo-
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for rustic, farmhouse, or Craftsman settings.
- · Measures 9-5/8-inch width by 8-1/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Antique Bronze (Painted) Construction: Steel Construction

Glass/Shade: Etched Seeded glass Panel



Square: 9-5/8 in Height: 8-1/8 in Depth: 10-3/8 in H/CTR: 2-1/4 in

Etched Seeded glass Panel

Width: 7-5/16 in Height: 3-15/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.375" W., 6.75" ht., 0.75" depth			