PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P560156-020 Barlowe

Transform you home into a warm and cozy dream with the friendly farmhouse-style of this small wall lantern. A rustic X-brace design decorates each side of the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality. An antique bronze finish complemented with antique copper accents adds warmth and character as the lantern infuses your home with gentle illumination.

- · Clear seeded glass panes add an extra pop of rustic personality.
- An antique bronze finish complemented with antique copper accents adds warmth and character as the lantern infuses your home with gentle illumination.
- A rustic X-brace design decorates each side of the charming lantern silhouette.
- Ideal for any bedroom, foyer, entryway, porch, or patio.
- · Perfect for rustic and farmhouse settings.

Finish: Antique Bronze (Painted)

Category: Outdoor

- Measures 6-1/2-inch width by 13-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.

Construction: Aluminum and Steel Construction Glass/Shade: Clear Seeded glass Panel

• Progress Lighting products are designed for exceptional quality, reliability, and functionality.



Width: 6-1/2 in Height: 13 in Depth: 7-1/2 in H/CTR: 2-3/8 in

Clear Seeded glass Panel Width: 4-1/8 in Height: 7-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	

Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth