PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:

P560156-135 Barlowe

Transform you home into a warm and cozy dream with the friendly farmhouse-style of this small wall lantern. A rustic X-brace design decorates each side of the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality. A stainless steel finish complemented with white accents adds warmth and character as the lantern infuses your home with gentle illumination.

- · Clear seeded glass panes add an extra pop of rustic personality.
- A stainless steel finish complemented with antique copper accents adds warmth and character as the lantern infuses your home with gentle illumination.
- A rustic X-brace design decorates each side of the charming lantern silhouette.
- $\cdot\,$ Ideal for any bedroom, foyer, entryway, porch, or patio.
- · Perfect for rustic and farmhouse settings.
- · Measures 6-1/2-inch width by 13-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Stainless Steel (Painted Clear Coat) Construction: Aluminum, Steel and Stainless Steel Construction Glass/Shade: Clear Seeded glass Panel



Width: 6-1/2 in Height: 13 in Depth: 7-1/2 in H/CTR: 2-3/8 in

Clear Seeded glass Panel Width: 4-1/8 in Height: 7-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Canopy covers a standard 4"	120 V	E26 base Porcelain socket	

recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth