

Project:			
Fixture Type:			
Location:			
Contact:			

P560157-020

Barlowe

Transform you home into a warm and cozy dream with the friendly farm-house-style of this small wall lantern. A rustic X-brace design decorates each side of the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality. An antique bronze finish complemented with white accents adds warmth and character as the lantern infuses your home with gentle illumination.

- Clear seeded glass panes add an extra pop of rustic personality.
- An antique bronze finish complemented with antique copper accents adds warmth and character as the lantern infuses your home with gentle illumination.
- A rustic X-brace design decorates each side of the charming lantern silhouette.
- · Ideal for any bedroom, foyer, entryway, porch, or patio.
- · Perfect for rustic and farmhouse settings.
- · Measures 7-1/2-inch width by 16-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Aluminum and Steel Construction

Glass/Shade: Clear Seeded glass Panel



Width: 7-1/2 in Height: 16 in Depth: 8-1/2 in H/CTR: 3-1/2 in

Clear Seeded glass Panel

Width: 5 in Height: 9-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth			