

Project:		
Fixture Type:		
Location:		
Contact:		

## P560157-135

## **Barlowe**

Transform you home into a warm and cozy dream with the friendly farm-house-style of this small wall lantern. A rustic X-brace design decorates each side of the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality. A stainless steel finish complemented with white accents adds warmth and character as the lantern infuses your home with gentle illumination.

- · Clear seeded glass panes add an extra pop of rustic personality.
- A stainless steel finish complemented with white accents adds warmth and character as the lantern infuses your home with gentle illumination.
- A rustic X-brace design decorates each side of the charming lantern silhouette.
- · Ideal for any bedroom, foyer, entryway, porch, or patio.
- · Perfect for rustic and farmhouse settings.
- · Measures 7-1/2-inch width by 16-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Stainless Steel (Painted

Clear Coat)

Construction: Aluminum, Steel and Stainless Steel Construction

Glass/Shade: Clear Seeded glass Panel



Width: 7-1/2 in Height: 16 in Depth: 8-1/2 in H/CTR: 3-1/2 in

Clear Seeded glass Panel

Width: 5 in Height: 9-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth			