

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560158-135 Barlowe

Transform your home into a warm and cozy dream with the friendly farmhouse-style of this small wall lantern. A rustic X-brace design decorates each side of the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality. A stainless steel finish complemented with white accents adds warmth and character as the lantern infuses your home with gentle illumination.

- Clear seeded glass panes add an extra pop of rustic personality.
- A stainless steel finish complemented with white accents adds warmth and character as the lantern infuses your home with gentle illumination.
- A rustic X-brace design decorates each side of the charming lantern silhouette.
- Ideal for any bedroom, foyer, entryway, porch, or patio.
- Perfect for rustic and farmhouse settings.
- Measures 9-1/8-inch width by 19-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

**Category:** Outdoor

**Finish:** Stainless Steel (Painted Clear Coat)

**Construction:** Aluminum, Steel and Stainless Steel Construction

**Glass/Shade:** Clear Seeded glass Panel



Width: 9-1/8 in  
Height: 19 in  
Depth: 10 in  
H/CTR: 3-1/2 in

Clear Seeded glass Panel  
Width: 6-3/8 in  
Height: 11-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	One 100 W max. Medium Base or LED equivalent	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth	120 V	E26 base Porcelain socket	