

Project:			
Fixture Type:			
Location:			
Contact:			

P560160-020

Trellis

Create a home that is undeniably beautiful with the intricate craftsmanship of this nature-inspired wall lantern. Beautiful white art glass panels serve as a backdrop to carefully crafted twig silhouettes. The panels are housed in a handsome antique bronze frame that will capture the gazes and hearts of both family members and guests.

- Beautiful white art glass panels serve as a backdrop to carefully crafted twig silhouettes.
- The panels are housed in a handsome antique bronze frame that will capture the gazes and hearts of both family members and guests.
- Create a home that is undeniably beautiful with the intricate craftsmanship of this-nature-inspired wall lantern.
- · Ideal for any entryway, porch, or patio.
- · Perfect for rustic or Craftsman settings.
- Measures 7-1/2-inch width by 12-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Antique Bronze (Painted) **Construction:** Steel Construction

Glass/Shade: White Art glass Panel, White Art glass Panel



Width: 7-1/2 in Height: 12-1/2 in Depth: 7 in H/CTR: 6 in

White Art glass Panel Width: 5-1/8 in Height: 10-5/8 in

White Art glass Panel Width: 5-11/16 in Height: 10-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
1/8 IP mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.75" ht., 1" depth			