

Project:			
Fixture Type:			
Location:			
Contact			

P560163-031

Seagrove

Capture the raw strength and captivating honesty of salty seashores with this coastal-inspired wall lantern. Clear seeded glass panes rest in a non-metallic, corrosion-resistant composite polymer with a rich black finish. An x-brace design adorns each side of the frame and adds an extra pinch of rustic character. DURASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- Clear seeded glass panes capture the raw strength and captivating honesty of salty seashores.
- The glass panes rest in a non-metallic, corrosion-resistant composite polymer frame with a rich black finish.
- An x-brace design adorns each side of the frame and adds an extra pinch of rustic character.
- Ideal for any bedroom, foyer, entryway, porch, or patio in farmhouse or coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a
 composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust,
 corrosion, and fading.
- Measures 5-1/2-inch width by 10-1/2-inch height.
- Uses one medium base bulb that is sold separately (40w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- $\bullet \ \ \text{Progress Lighting products are designed for exceptional quality, reliability, and functionality. }$

Category: Outdoor **Finish:** Black (Painted)

Construction: Composite Polymer Construction Glass/Shade: Clear Seeded glass Panel



Width: 5-1/2 in Height: 10-1/2 in Depth: 7-1/2 in H/CTR: 3-1/4 in

Clear Seeded glass Panel

Width: 5 in Height: 5-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CETLus Wet Location Listed
		One 40 W max. Medium Base or	
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	5-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4"			
recessed outlet box: 5" W., 5" ht.,			
1.125" depth			