

Project:			
Fixture Type:			
Location:			
Contact:			

P560168-031Port Royal

This wall lantern distills both industrial and artisan influences with its signature ribbed black frame constructed from durable corrosion-resistant, composite polymer. Inside the cage rests an elongated, clear glass shade that adds to the light fixture's modern flair. The design's blend of industrial and coastal inspiration makes it a perfect light fixture for updating your favorite spaces in and around your home. DURASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- Inside the fixture's ribbed frame rests an elongated, clear glass shade that adds to the light fixture's modern flair.
- A signature ribbed black frame constructed from durable corrosion-resistant, composite polymer materials distills both industrial and artisan influences.
- The design's blend of industrial and coastal inspiration makes it a perfect light fixture for updating your favorite spaces in and around your home.
- Ideal for any foyer, bedroom, entryway, porch, or patio in urban industrial, farmhouse, or coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a
 composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust,
 corrosion, and fading.
- Measures 6-1/4-inch width by 12-1/2-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- $\boldsymbol{\cdot}$ Includes installation instructions and mounting hardware.
- $\bullet \ \ \text{Progress Lighting products are designed for exceptional quality, reliability, and functionality.}$

Category: Outdoor **Finish:** Black (Painted)

Construction: Composite Polymer Construction **Glass/Shade:** Clear glass Cylindrical Shade



Width: 6-1/4 in Height: 12-1/2 in Depth: 7-1/2 in H/CTR: 2-1/2 in

Clear glass Cylindrical Shade

Width: 4-5/8 in Height: 9-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CETLus Wet Location Listed
Wan moantoa		One 60 W max. Medium Base or	02.1240 7701 2004 2.0104
Swivel mounting strap for outlet	6 inches of wire supplied	LED equivalent	5-year Limited Warranty
box included		•	. .
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4"			
recessed outlet box: 5" W., 6.25"			
ht., 1" depth			