



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560169-031 Ellery

Ellery Collection One-Light Black Modern Farmhouse Outdoor Wall Lantern

Category: Outdoor

Finish: Black (Powder Coat)

Construction: Cast Aluminum Housing

Glass/Shade: Etched Opal Glass Square/Rectangular



Width: 7 in
 Extends: 6-3/4 in
 Height: 12-1/8 in
 H/CTR: 9-7/8 in

Etched Opal Glass Square/Rectangular
 Width: 6-1/8 in
 Height: 10-15/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 6.312" ht., 0.812" depth		Fully dimmable with dimmable bulbs.	