

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

**P560170-031**  
**Ellery**

Ellery Collection One-Light Black Modern Farmhouse Large Outdoor Wall Lantern

**Category:** Outdoor  
**Finish:** Black (Powder Coat)  
**Construction:** Cast Aluminum Housing  
**Glass/Shade:** Etched Opal Glass Square/Rectangular



Width: 8.5 in  
 Extends: 7-5/8 in  
 Height: 15-1/4 in  
 H/CTR: 12-7/8 in

Etched Opal Glass Square/Rectangular  
 Width: 7-3/8 in  
 Height: 14-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 6.31" ht., 0.812" depth		Fully dimmable with dimmable bulbs.	