

Project:			
Fixture Type:			
Location:			
Contact			

P560173-031 Marguette

This wall lantern is a go-to choice when incorporating classic silhouettes with a farmhouse flair into your home décor vision. The traditional frame is constructed with non-metallic, corrosion-resistant composite polymer in a classic black finish. A beautiful water glass shade adds charming character to the timeless design. DURASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- · A beautiful water glass shade adds charming character to the timeless design.
- The traditional frame is constructed with non-metallic, corrosion-resistant black composit polymer finish.
- The wall lantern is a go-to choice when incorporating classic silhouettes with a farmhouse flair into your home décor vision.
- Ideal for any bedroom, foyer, entryway, porch, or patio in transitional, traditional, and coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a
 composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust,
 corrosion, and fading.
- Measures 10-1/8-inch width by 18-5/8-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear Water glass Panel



Width: 10-1/8 in Height: 18-5/8 in Depth: 12-1/2 in H/CTR: 7-5/8 in

Clear Water glass Panel

Width: 7-3/4 in Height: 10-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CETLus Wet Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	5-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 6.5" W., 9.75" ht., 1.5" depth			