



Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P560178-031 Benton Harbor

Benton Harbor Collection One-Light Medium Wall Lantern with DURASHIELD

Category: Outdoor

Finish: Textured Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear Glass Shade

Width: 7-1/2 in
Depth: 8-5/8 in
Height: 11 in
H/CTR: 2-5/8 in

Clear Glass Shade
Width: 6-5/8 in
Height: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	(1) Medium Base (E26) socket	cETLus Wet Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	Lamp Type A19	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 1" depth	120 V	Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
		Fully dimmable with dimmable bulbs.	