

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560185-031 Benton Harbor

This wall lantern is expertly crafted with that casual, coastal style you love. A clear glass shade shields a simple light base for a seaside-living vibe. The shade is cradled inside an open-cage black frame featuring thin bars and constructed with a composite polymer, corrosion-resistant housing. DURASHIELD by Progress Lighting is built to last. Constructed from a composite material with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance finish has a 5-year warranty and is resistant to rust, corrosion, and fading.

- A clear glass shade shields a simple light base for a seaside-living vibe.
- The glass shade is cradled inside an open-cage black frame of corrosion-proof composite polymer.
- The wall lantern is constructed with a non-metallic, corrosion-resistant housing.
- Ideal for any foyer, bedroom, entryway, porch, or patio in transitional or coastal settings.
- DURASHIELD by Progress Lighting is a material that is built to last. Constructed from a composite polymer with UV protection, DURASHIELD holds up even in the harshest weather conditions. This high-performance material has a 5-year warranty and is resistant to rust, corrosion, and fading.
- Measures 8-3/4-inch width by 13-inch height.
- Uses one medium base bulb that is sold separately (100w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor

Finish: Black (Painted)

Construction: Composite Polymer Construction

Glass/Shade: Clear glass Shade



Width: 8-3/4 in
Height: 13 in
Depth: 9-5/8 in
H/CTR: 2-5/8 in

Clear glass Shade
Width: 7-7/8 in
Height: 8-3/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CETLus Wet Location Listed
Mounting plate for outlet box included	6 inches of wire supplied	One 100 W max. Medium Base or LED equivalent	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 1" depth	120 V	E26 base Porcelain socket	