

## Z-1080 LED

Wall vertical only Mounted • Wet Location Listed **PROGRESS LED**

### Description:

Z-1080 LED Collection Black One-Light Small LED Outdoor Sconce

### Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W, 12.5 in ht., 1.875 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Number of Modules	1
Input Power	11 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	415/37 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed Meets California Title 24 JA8-2019

## P560210-031-30



### Dimensions:

Width: 5 in  
 Depth: 3 in  
 Height: 13 in  
 H/CTR: 6-1/2 in

White Acrylic Diffuser  
 Width: 4-1/8 in  
 Height: 12-1/8 in



# P560210-031-30

## Dimming Notes:

---

P560210-031-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Leviton\_IPI06-1LZ

Leviton\_SureSlide 6674

Lutron\_Nova T VTELV-300

Lutron\_Diva DVELV-300P

Lutron\_Ariadni AYCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.