

Project:
Fixture Type:

Location:
Contact:

Z-2020 LED

Ceiling Mounted • Wet Location Listed PROGRESS LED



Description:

Z-2020 LED Collection 1-Light Satin White Frosted Glass LED Modern Circle Wall Light

Specifications:

- · Frosted Glass Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W., 0.75 in ht., 4.75 in depth
- · Mounting strap for outlet box included
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

Performance:

Ni washan af Madulaa	1
Number of Modules	I
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	670/71 (LM-82)
ССТ	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P560260-028-30



Dimensions:

Length: 6-1/4 in Extends: 2-1/4 in Height: 2-1/4 in

Frosted Glass Cylindrical

Width: 1-1/4 in Height: 4-3/4 in



Z-2020 LED

Ceiling Mounted • Wet Location Listed PROGRESS LED



Dimming Notes:

 $P560260\mbox{-}028\mbox{-}30$ is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva_DVELV-300P

Lutron_Nova_T_NTELV-300

Lutron_Caseta_

Lutron_Ariadni_AY-600P

Leviton_Illumatech_IPI06-1LZ

Leviton_SureSlide_6672

Lutron_Ariadni_AYCL-153P

Lutron_Skylark_Contour_CTCL-153P

Lutron_Diva_DVCL-153P

Lutron_Toggler_TGCL-153P

Lutron_Maestro_MACL-153M

Lutron_Ariadni_AYLV-600P

Lutron_NOVA_T_NTLV-600

 $lutron_Maestro_MAELV-600$

Lutron_spacer/system_SPSELV-600

Lutron_Renoir_II_AWRMG-EAW

Lutron_Nova_N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P560260-028-30