PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

P560261-031 Wakeford

Wakeford One-Light Textured Black Transitional Outdoor Small Wall Lantern

Category: Outdoor Finish: Textured Black (Painted) Construction: Steel Construction Glass/Shade: Clear Water Glass Panel



Width: 8 in Extends: 5-3/4 in Height: 17-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.875" W., 10.625" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
		bulbs	