



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560267-108 Stature

Stature Collection 1-Light Oil Rubbed Bronze Clear Glass Transitional Outdoor Small Wall Lantern Light

Category: Outdoor
Finish: Oil Rubbed Bronze (Painted)
Construction: Aluminum Construction
Glass/Shade: Clear Glass Panel, Clear Glass Panel



Length: 6 in
 Extends: 5-3/8 in
 Height: 11-1/2 in
 H/CTR: 5-1/4 in

Clear Glass Panel
 Width: 0-1/8 in
 Height: 10-3/16 in

Clear Glass Panel
 Width: 0-1/8 in
 Height: 11.06 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: one 60 W max.	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 V	E12 base Porcelain Socket	1-year Limited Warranty
Backplate covers a standard 4" recessed outlet box: 4.312" W., 11.12" ht., 0.5" depth			