

Project:

Fixture Type:

Location:

Contact:

P560268-108 Stature

Stature Collection 2-Light Oil Rubbed Bronze Clear Glass Transitional Outdoor Medium Wall Lantern Light

Category: Outdoor

Finish: Oil Rubbed Bronze (Painted) **Construction:** Aluminum Construction

Glass/Shade: Clear Glass Panel, Clear Glass Panel



Length: 8 in Extends: 5-7/8 in Height: 16 in H/CTR: 8 in

Clear Glass Panel Width: 0-1/8 in Height: 14-5/8 in

Clear Glass Panel Width: 0-1/8 in Height: 15-9/16 in

		Height: 15-9/16 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 60 W max.	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 V	E12 base Porcelain Socket	1-year Limited Warranty
Backplate covers a standard 4" recessed outlet box: 6.12" W., 15.68" ht., 0.5" depth			