

Project:

Fixture Type:

Location:

Contact:

## P560269-108 Stature

Stature Collection 2-Light Oil Rubbed Bronze Clear Glass Modern Outdoor Large Lantern Light

Category: Outdoor

**Finish:** Oil Rubbed Bronze (Painted) **Construction:** Aluminum Construction

Glass/Shade: Clear Glass Panel, Clear Glass Panel



Length: 9 in Extends: 5-7/8 in Height: 21 in H/CTR: 10-1/2 in

Clear Glass Panel Width: 0-1/8 in Height: 19-5/8 in

Clear Glass Panel Width: 0-1/8 in Height: 20-9/16 ir

	Height: 20-9/16 in		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 60 W max.	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 V	E12 base Porcelain Socket	1-year Limited Warranty
Backplate covers a standard 4" recessed outlet box: 7.5" W., 20.52" ht., 0.5" depth			