

Project:

Fixture Type:

Location:

Contact:

P560272-031 Belden

Belden Collection One-Light Black Modern Farmhouse Outdoor Wall Lantern

Category: Outdoor

Finish: Black (Powder Coat)

Construction: Cast Aluminum Housing **Glass/Shade:** Clear Seeded Glass Cylindrical



Width: 7 in Extends: 9 in Height: 14-3/8 in H/CTR: 11 in

Clear Seeded Glass Cylindrical

Width: 5-7/8 in Height: 11-7/8 in

		8 71	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 7" ht.,		LED: 17.5-watt MAX per socket	
1.12" depth		Dimmable to 10% brightness (See Dimming Notes)	