

Project:		
Fixture Type:		
Location:		
Contact:		

P560287-031 Walcott

Walcott One-Light Textured Black Modern Farmhouse Outdoor Large Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Aluminum Construction
Glass/Shade: Clear Glass Panel



Width: 8-1/4 in Extends: 8-1/4 in Height: 20 in H/CTR: 4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 10"		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
ht., 0.75" depth		Fully dimmable with dimmable bulbs	