PROGRESS LIGHTING[™]

Project:

Fixture Type:

Location:

Contact:



5" Outdoor Up/Down Wall Cylinder Two-Light Modern Black Outdoor Wall Lantern with Top Lens

Category: Outdoor Finish: Black (Powder Coat) Construction: Aluminum Housing



Length: 5 in Extends: 7-15/16 in Height: 14 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type PAR30	1-year Limited Warranty
		Incandescent: 75-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.45" W., 4.45" ht., 0.65" depth		LED: 15-watt MAX per socket	
		Fully dimmable with dimmable bulbs	