

Project:

Fixture Type:

Location:

Contact:

P560292-020 6IN CYL RNDS

6" Outdoor Up/Down Wall Cylinder Two-Light Modern Antique Bronze Out-door Wall Lantern with Top Lens

Category: Outdoor

Finish: Antique Bronze (Powder Coat) **Construction:** Aluminum Housing



Length: 6 in Extends: 8-15/16 in Height: 18 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type PAR38 250 W	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.45" W., 4.45" ht., 0.65" depth		Fully dimmable with dimmable bulbs	