



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560292-031 6IN CYL RNDS

6" Outdoor Up/Down Wall Cylinder Two-Light Modern Black Outdoor Wall Lantern with Top Lens

Category: Outdoor
Finish: Black (Powder Coat)
Construction: Aluminum Housing



Length: 6 in
Extends: 8-15/16 in
Height: 18 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type PAR38 250 W	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.45" W., 4.45" ht., 0.65" depth		Fully dimmable with dimmable bulbs	