

Project:		
Fixture Type:		
Location:		
Contact:		

P560296-031 Ward

Ward Collection One-Light Textured Black Urban Industrial Outdoor Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Aluminum Construction
Glass/Shade: Textured Black Metal Cone



Width: 7-7/8 in Extends: 9-1/8 in Height: 7-3/8 in H/CTR: 4-7/8 in

Textured Black Metal Cone

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 1.12" ht., 5" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	Yes, per photometry (not registered with IDA)
.,,		Fully dimmable with dimmable bulbs	