## progress lighting DESIGN**+SERIES**™

Project:			
Fixture Type:			
Location:			
Contact:			

## P560297-108 Point Dume-Seamoor

Jeffrey Alan Marks Point Dume Seamoor Oil Rubbed Bronze Outdoor Wall Lantern

Category: Outdoor Finish: Oil Rubbed Bronze (Painted) Construction: EPMM Construction Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Flat Square/ Rectangular



Width: 11 in Extends: 6 in Height: 12-5/8 in H/CTR: 7-1/2 in

Clear Glass Flat Square/Rectangular Width: 8-1/16 in Height: 9-7/16 in

Clear Glass Flat Square/Rectangular Width: 4 in Height: 9-7/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 8.5" W., 9.62" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	