

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560297-141 Point Dume™-Seamoor

Point Dume Seamoor Galvanized Finish Outdoor Wall Lantern

Category: Outdoor
Finish: Galvanized Finish (Painted)
Construction: EPMM Construction
Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Flat Square/Rectangular



Width: 11 in
Extends: 6 in
Height: 12-5/8 in
H/CTR: 7-1/2 in

Clear Glass Flat Square/Rectangular
Width: 8-1/16 in
Height: 9-7/16 in

Clear Glass Flat Square/Rectangular
Width: 4 in
Height: 9-7/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 8.5" W., 9.62" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	