## PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

## P560301-031 Precinct

Precinct Collection One-Light Textured Black Urban Industrial Outdoor Wall Lantern

## Category: Outdoor Finish: Textured Black (Painted) Construction: Steel Construction Glass/Shade: Textured Black Metal Cone



Width: 8 in Extends: 9.5 in Height: 9.5 in H/CTR: 6-3/4 in

Textured Black Metal Cone

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 0.81" ht., 5" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	Yes, per photometry (not registered with IDA)
		Fully dimmable with dimmable bulbs	