

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560302-141 Point Dume-Dunemere

Jeffrey Alan Marks Point Dume Dunemere Galvanized Finish Outdoor Wall Lantern

Category: Outdoor

Finish: Galvanized Finish (Painted)

Construction: EPMM Construction

Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 6-5/8 in
 Extends: 5-7/8 in
 Height: 10-1/2 in
 H/CTR: 7-5/8 in

Clear Glass Flat Square/Rectangular
 Width: 4-1/8 in
 Height: 6-7/16 in

Clear Glass Panel
 Width: 4-1/2 in
 Height: 8-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.625" W., 8.875" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	